

Product Brochure For W122

## Mini Argon + CO2 Gas Disposable Cylinder - Ar/O2

60 Litres  
 Special Courier



ORDER CODE:	W122
MODEL:	Argon + CO2
Type:	60 Litres
Clamping Capacity:	Special Courier
Locking Handle - Pivot Movement:	~
Clamp Bar - Pivot Movement:	~
Plunger Travel (mm):	~
Throat Depth (mm):	~
Opening (mm):	~
Size:	~
Quantity Per Pack (No.):	~
Clamping Force (kg):	~
Over all Length (mm):	~
Nett Weight (kg):	~



### Description

Argon - This gas is used for MIG welding aluminium. It can also be used for general TIG welding.

Avoid costly rental payments for large gas bottles and increase the portability of your MIG machine by using a disposable gas bottle. If you want to change to weld mild steel, simply use the CO2 or Argon CO2 mix gas with mild wire.

Pressurised container:

- Use with care and do not expose to the sun or temperatures exceeding 50 deg.C
- Keep out of children's reach
- It cannot be reused
- Dispose of it correctly
- Connect to the regulator and seal by hand only
- Never drop oil or grease into the connection or regulator.

WARNING: Non refillable bottle

### DIRECTIONS FOR USE

Remove protective plastic cap from top of the bottle. Screw the gas bottle regulator down (clockwise) onto the bottle. Do not force or over tighten. If the gas does not flow, remove and re-fit the regulator. After use un-screw the regulator. The bottle is self-sealing.

### Features

- ARGON 86% + CO2 14%
- TARE: 1120G
- VOLUME: 950cc
- PRESSURE: 60 Bar
- CONTENTS: 60 Litres
- TEST PRESSURE: PH 165 Bar
- UN. Nr. 1006 - Class / DIV. 2.2 ARD/RID 2,1A

Product Brochure For W122

---

**Specific Features**



Packaging

**Recommended Accessories**

O0171

Argon Gas Regulator

